

# Broadcast and Professional Monitors BVM-D Series

# Defining Digital @Sony

Sony's legendary line of broadcast monitors now has a new family of additions. The BVM-D series digital monitors are optimized for the DTV world. They support 480I, 480P, 720P and 1080I inputs directly, with no need for a scan converter. They display each input signal at its native frequency and resolution with an extremely high degree of color accuracy. And they incorporate the patented, award-winning Trinitron<sup>®</sup> CRT system to deliver uncompromising quality and detail.

# Multiformat Signal Support

These monitors accept the wide variety of digital signals necessary to allow you the freedom to produce in whatever format you choose: 480I, 480P, 720P or 1080I.

# Sony Technology

To provide the highest possible picture quality, all BVM monitors are equipped with CRTs manufactured by Sony, using SMPTE-C standard phosphors\*. New flat surface 16:9 aspect HR Trinitron CRTs have been developed exclusively for the BVM-D32E1WU and BVM-D24E1WU.

\* P-22 phosphors are used in the BVM-D9H1U/D9H5U.

# Functionality

This new BVM monitor series can be used in a variety of applications.

- Master monitors: BVM-D32E1WU/ BVM-D24E1WU/D20F1U
- Picture monitors: BVM-D14H1U/D14H5U/ D9H1U/D9H5U
- Field use: BVM-D9H1U/D9H5U



# Line-up

# A Complete line-up of DTV Ready Monitors

Designed specifically to meet your diverse DTV requirements, while also supporting the interfaces, infrastructures, and archival formats you are using now.

Only Sony can provide you with the complete line-up — from 32" master monitors to 9" picture and field-use monitors — that you will need as you make your transition to digital. And only Sony provides the technology to enable you to continue using your current monitors next to your new digital monitors in one integrated system.

# Master Monitor

- 32", 24" and 20" monitors\*
- Newly developed flat surface, 16:9 aspect HR Trinitron CRTs for the 32" and 24" master monitors
- $\bullet$  Resolution of 1000 TV lines (32" and 24" in 4:3/16:9 modes) and 900/700 TV lines (20" in 4:3/16:9 modes)



BVM-D24E1WU display unit with optional BKM-10R and BKM-34H attached

# Picture Monitor

- 14" and 9" monitors\*
- Display unit (BVM-D14H1U/D9H1U) and stand-alone (BVM-D14H5U/D9H5U) monitors for greater flexibility in system integration
- Resolution of 800/600 TV lines (14" in 4:3/16:9 modes) and 450/340 TV lines (9" in 4:3/16:9 modes)



BVM-D14H5U stand-alone monitor

# Field Use

- 9" monitors\*
- · Optional lithium-ion battery packs available for added convenience
- Optional Monitor ENG kit (hood and rear protector) available
- Audio capability, built-in speaker, and simple stand for added versatility in the field (BVM-D9H5U only)



BVM-D9H5U stand-alone monitor with optional VF-508 Monitor ENG kit

# **BVM-D Series Monitor Features**

# **Multiformat Signal Support**

All of these monitors accept signals with a frequency range of 15.625 kHz to 45 kHz, and each picture signal is directly scanned


from the original signal using the point scan method to achieve high picture quality.

## **Acceptable Formats**

System	Horizontal scanning frequency	Total lines per frame	Active lines per frame	Frame rate* (Hz)	Scanning format	Aspect	Standard
575/50I (PAL)	15.625	625	575	25	2:1 Interlace	16:9 / 4:3	ITU 601
480/60I (NTSC)	15.734	525	483	30	2:1 Interlace	16:9 / 4:3	ITU 601
575/50P	31.250	625	575	50	Progressive	16:9 / 4:3	_
480/60P	31.469	525	483	60	Progressive	16:9 / 4:3	SMPTE 293M
1080/24PsF	27.000	1125	1080	24	2:1 Interlace	16:9	_
1080/50I	28.125	1125	1080	25	2:1 Interlace	16:9	SMPTE 274M
1035/60I	33.750	1125	1035	30	2:1 Interlace	16:9	BTA S-001B
1080/60I	33.750	1125	1080	30	2:1 Interlace	16:9	SMPTE 274M / BTA S-001B
720/60P	45.000	750	720	60	Progressive	16:9	SMPTE 296M

\* Each of the frame rates is also compatible with 1/1.001.

## **System Integration**



Only the Sony BVM-D series provides you with models ranging from 9" to 32" that can be controlled in one completely integrated, multicontrol system. And, your current E, F, and G series BVM monitors and HDM series monitors can also be controlled in the same system.

## **Superb Picture Reproduction**

- HR Trinitron provides high resolution pictures
- SMPTE-C standard phosphors\*
- Sony manufactured CRTs provide excellent color uniformity and performance
- Beam current feedback for stable color temperature
- \* P-22 phosphors are used in the BVM-D9H1U/D9H5U.

- Modular design with separate display and control units
- Parallel and RS-485 serial remote control capability
- Up to 32 monitors can be controlled with one control unit
- Optional rack mounting kits

## **Auto Set-up Capabilities**

- Built-in auto set-up system for chroma, phase, and white balance
- Precise color temperature adjustment using external color probes: Sony BKM-14L, Graseby SLS 9400, Minolta CA-100, Philips PM 5639, Thoma TF6
- Adjustable color temperature (factory preset to D65)

Aspect Ratio

The BVM-D32E1WU/D24E1WU, with their 16:9 CRTs, are capable of displaying both 16:9 and 4:3 formats. The other models are all equipped with 4:3 CRTs that are also capable of displaying the 16:9 formats. 16:9 and 4:3 aspect ratio masks are supplied with the 20", 14" and 9" models.



Interchangeable 16:9 and 4:3 aspect ratio masks

# Features

# 32", 24" and 20" Monitor Features

- Flat surface, 16:9 aspect ratio HR Trinitron CRTs developed specifically for the BVM-D32E1WU and BVM-D24E1WU
- Optional BKM-12Y Memory Card for storage and recall of primary set-up data
- Safe area display, 4:3 area marker (line, translucent mat, full black mat)
- Data transfer between monitors using an optional BKM-12Y Memory Card or via an RS-485 link
- ISR (Interactive Status Reporting) for system diagnostics
- Built-in test signal generator for crosshatch, 100% white signal, 20% gray signal, gray scale, and PLUGE




Flat surface, 16:9 aspect ratio HR Trinitron CRT

# **On-screen Menus for Adjustment and Operation**

#### **Input Configuration**

Depending on the optional boards installed, the settings for the type and location of the input signals can be made from the Input Configuration menu.



#### Beam Landing Correction (BVM-D32E1WU/D24E1WU)

The BVM-D32E1WU and BVM-D24E1WU are capable of correcting beam landing shift which may occur as a result of the terrestrial magnetic field. This correction can be made manually or automatically, with the use of the optional BKM-14L Auto Set-up Probe.

MANUAL		
DIRECTION	EAST	
FINE ADJUST		
NS	100	
TOP LEFT	100	
TOP RIGHT	100	
BOTTOM LEFT	100	
BOTTOM RIGHT	100	
RESET		

#### Matrix Interchangeability

Depending on the input signal, one of three matrices (ITU 601, ITU 709, or SMPTE 240M) can be chosen from the Matrix menu.

	MATRIX	
1080/60I	ITU	709
1080/50I	ITU	709
1080/48I	ITU	709
1035/60I	SMPTE	240M
720/60P	ITU	709
575/50P	ITU	601
575/50I	ITU	601
480/60P	ITU	601
480/60I	ITU	601

#### Digital Uniformity (BVM-D32E1WU/D24E1WU)

White can be reproduced uniformly on every point of the screen, even in the peripheral area, through the digital uniformity circuit. This adjustment can be made manually or automatically, with the use of the optional BKM-14L Auto Set-up Probe.

WHITE UNIFORMITY (2/2) 1080/60I 16:9-UNDR	
Digital Uniformity ADJ Manual Auto Full Points ONE Point	
ORIGINAL VALUE 1080/601 16:9-NORM SIGNAL EXT	

#### Digital Convergence (BVM-D32E1WU only)

The BVM-D32E1WU is capable of adjusting the convergence at each point of the screen, even in the peripheral area, through the digital convergence circuit. Using the onscreen menu, adjustments can be made to meet any installation.

> CONU FINE ADJUST 1080/601 16:9-NORM ADJUST... H CONU :CONTRAST KNOB H G CONU :BRIGHT KNOB U CONU :CHROMA KNOB U G CONU :PHASE KNOB

CURSOR POSITION :10KEY TO CANCEL :MENU KEY TO CONFIRM :ENTER KEY

# Decoder and Expansion Boards for 32", 24" and 20" Monitors

The BVM-D32E1WU, BVM-D24E1WU and BVM-D20F1U are equipped as standard with Analog Component (Y/PB/PR, GBR) input/output connectors and four option slots in the rear panel of the monitor. Depending on the particular system requirements, the most appropriate boards can simply be inserted in the option slots in the rear panel of the monitor. A range of input decoder and expansion boards is available to provide

many different input configurations. Although each decoder board has a primary function, when two or more boards are installed at the same time, they combine to accept a much wider range of signal inputs and standards.



BVM-D24E1WU with optional decorder and expansion boards

## Separate Control and Display Units

The 32", 24" and 20" monitors are designed as display units. However, an optional BKM-10R Control Unit can be easily attached to the 24" and 20" monitors with optional attachment kits.



BVM-D20F1U with optional BKM-10R and BKM-32H attached

### **Input Decorder and Expansion Board Configurations**

-							-					
Signal format	Adaptor name	BKM-41HD HD SDI Input Adaptor	BKM-42HD HD SDI Input Adaptor	BKM-48X* HD Analog Input Expansion Adaptor	BKM-20D SDI 4:2:2 Decoder Adaptor	BKM-21D SDI Multi Decoder Adaptor	BKM-22X SDI Input Expansion Adaptor	BKM-24N NTSC Decoder Adaptor	BKM-25P PAL Decoder Adaptor	BKM-26M PAL-M Decoder Adaptor	BKM-27T Tri-Standard Decoder Adaptor	BKM-28X Analog Input Expansion Adaptor
Serial	Component 525/625	-	-	-	O	O	0	-	-	-	-	-
digital	Composite NTSC	-	-	-	0	0	0	-	-	-	-	-
input	Composite PAL	-	-	-	0	0	0	-	-	-	-	-
	575/50P	-	-	-	-	-	-	-	-	-	-	-
	480/60P	-	-	-	-	-	-	-	-	-	-	-
	1080/24PsF	O	O	-	-	-	-	-	-	-	-	-
	1080/50I	0	O	-	-	-	-	-	-	-	-	-
	1035/60I	0	O	-	-	-	-	-	-	-	-	-
	1080/60I	O	O	-	-	-	-	-	-	-	-	-
	720/60P	O	O	-	-	-	-	-	-	-	-	-
Analog	Composite NTSC	-	-	0	0	0	0	0	0	0	O	0
input	Composite PAL	-	-	0	0	0	0	0	0	0	O	0
	Composite PAL-M	-	-	0	0	0	0	0	0	O	0	0
	Composite SECAM	-	-	0	0	0	0	0	0	0	0	0
	Y/PB/PR 525/625	0	O	O	O	0	O	0	0	O	0	0
	GBR 525/625	O	O	O	O	O	O	0	O	O	O	0
	Y/C NTSC	-	-	0	-	-	-	0	0	0	0	0
	Y/C PAL	-	-	0	-	-	-	0	O	0	O	0
	Y/C PAL-M	-	-	0	-	-	-	0	0	O	0	0
	Y/PB/PR, GBR 575/50P	O	0	O	-	-	-	-	-	-	-	-
	Y/PB/PR, GBR 480/60P	O	0	O	-	-	-	-	-	-	-	-
	Y/PB/PR, GBR 1080/24PsF	O	0	O	-	-	-	-	-	-	-	-
	Y/PB/PR, GBR 1080/50I	O	O	O	-	-	-	-	-	-	-	-
	Y/PB/PR, GBR 1035/60I	O	0	0	-	-	-	-	-	-	-	-
	Y/PB/PR, GBR 1080/60I	O	0	0	-	-	-	-	-	-	-	-
	Y/PB/PR, GBR 720/60P	O	0	O	-	-	-	-	-	-	-	-
Number of	digital inputs	1	2	-	3	3	3	-	-	-	-	-
Number of	analog inputs	1	1	6	3	3	3	6	6	6	6	6

\* Equipped with floating/non-floating ground mode selector for hum reduction.


Signal can be reproduced with this adaptor

O Signal can be reproduced when combined with an appropriate decoder

# Features

# 14" and 9" Monitor Features

- 4:3 area marker
- Conventional functions, H/V delay, Underscan, Blue only, Mono are available
- Equipped with three color Tally (Red, Green, Amber: R + G)
- Mountable into a 19-inch EIA standard rack with optional mounting brackets
- Copy function enables INPUT CONFIG and SYSTEM CONFIG settings to be copied from other BVM-D14H/ D9H monitors connected by serial remote
- Simplified menus for greater ease of use



- Audio capability and built-in speaker in the bottom of the monitor (BVM-D9H5U only)
- Equipped with simple stand (BVM-D9H5U only)
- Operate on three alternative power sources: AC power (supplied adaptor), external DC 12 V, optional Lithium-ion batteries BP-L60A/L90A (BVM-D9H1U/D9H5U only)



BVM-D9H5U with AC adaptor (left) and optional BP-L60A battery pack (right)

The chart below shows the operation times of the 9" monitors when run on batteries. Times may vary depending on the picture, condition of the battery and temperature.

		Inserted Input Adaptor			
	Battery	Analog Component BKM-129X	Full options (max) BKM-142HD + BKM-120D		
BVM-D9H1U/	BP-L60A	Approx. 90 min.	Approx. 60 min.		
BVM-D9H5U	BP-L90A	Approx. 150 min.	Approx. 100 min.		

## Input Boards for 14" and 9" Monitors

A new series of four input boards has been developed specifically for the 14" and 9" BVM-D series monitors. With three option slots, these monitors are able to accept a wide variety of input signals.



BVM-D14H1U with optional input boards

#### HD SDI Input Adaptor ◆ BKM-142HD - 2 HD SDI signal inputs/1 monitor out - Acceptable HD SDI signals: 1080/24PsF, 1080/50I, 1035/60I, 1080/60I, 720/60P - Power consumption: 9 W - Dimensions: 49.7 (W) x 161.4 (H) x 121.8 (D) mm (6 3/s at 4/s inches) - Mass: Approx. 730 g (1 lb 10 oz) \* This board occupies 2 slots

## SDI 4:2:2 Input Adaptor

- 2 D1 SDI signal inputs/2 active outputs with loop-through
   Power consumption: 4 W
- Power consumption:
   Dimonsions: 24.7 (W)
- Dimensions: 24.7 (W) x 161.4 (H) x 121.8 (D) mm
- (1 x 6 <sup>3</sup>/<sub>8</sub> x 4 <sup>7</sup>/<sub>8</sub> inches) - Mass: Approx. 310 g (11 oz)



- 2 Analog composite with loop-through BNC, Automatic 75  $\Omega$  termination/1 Y/C with loop-through Mini DIN 4-pin, Automatic 75  $\Omega$  termination
- Power consumption: 3 W
- Digital 3-lines Comb filter
- Dimensions: 24.7 (W) x 161.4 (H) x 121.8 (D) mm (1 x 6 <sup>3</sup>/<sub>8</sub> x 4 <sup>7</sup>/<sub>8</sub> inches)
- Mass: Approx. 270 g (10 oz)

## Analog Component Input Adaptor

- (supplied as standard with 14" and 9" monitors)
- 1 Analog component (Y/PB/PR, GBR) with loop-through BNC, Automatic 75  $\Omega$  termination/1 EXT SYNC with loop-through BNC, Automatic 75  $\Omega$  termination
- Power consumption: 0.5 W
- Dimensions: 24.7 (W) x 161.4 (H) x 121.8 (D) mm
- (1 x 6 3/8 x 4 7/8 inches)
- Mass: Approx. 250 g (9 oz)







# **Optional** Accessories



Central Control Unit **BKM-10R** 



19" EIA Standard Rack Mount Kit for 20" monitors **BKM-30E20** 



Control Unit Attachment Kit for BKM-10R with 24" monitor **BKM-34H** 



19" Rack Mount Kit for 9" monitors **MB-520** 



Hand-held Control Unit **BKM-11R** 



19" EIA Standard Rack Mount Kit for 14" monitors **BKM-31E14** 




Mounting Panel for EIA Standard Rack (5U) for 9" stand-alone monitors **MB-509** 



Memory Card **BKM-12Y** 



19" EIA Standard Rack Mount Kit for 14" stand-alone monitors **BKM-30E14** 



19" Rack Mount Kit for BKM-10R **MB-510** 



**BKM-14L** 



Control Unit Attachment Kit for BKM-10R with 20" monitor BKM-32H



Mounting Panel for EIA Standard Rack (4U) for 9" display unit monitors **MB-519** 



Rechargeable Lithium-ion Battery Packs for 9" monitors **BP-L60A/L90A** 





Monitor ENG Kit (Hood and Rear Protector) for 9" monitors **VF-508** 



9-pin Cable for RS-485/422 serial remote control RCC-5G/10G/30G

# **Specifications**

			BVM-D32E1WU	BVM-D24E1WU			
General	Signal for	mat	15.625 kHz to 45 kHz				
			(For more details, please refer to the Acceptable Formats table)				
	Type Desuge real	u inom on to	Displa 100 to 240 V AC				
		quirements nsumption (with options)	100 to 240 V AC 180 W (235 W max.)	± 10%, 50/ 60 Hz 155 W (205 W max.)			
	Dimension		794 (W) × 556.5 (H) × 694 (D)	565.5 (W) × 436.8 (H) × 587.3 (D)			
		all protruding parts) inches	$31^{3/8} \times 22 \times 27^{3/8}$	$\frac{22 3/8 \times 17 1/4 \times 23 1/8}{22 3/8 \times 17 1/4 \times 23 1/8}$			
	Mass	incirco	approx. 94 kg (206 lb 13 oz)	approx. 51 kg (112 lb 3 oz)			
	CRT	CRT type	32-inch HR Trinitron (flat surface, 16:9 aspect)	24-inch HR Trinitron (flat surface, 16:9 aspect)			
		AG pitch	0.32–0.36 mm, 90° deflection, Ø29.1 mm in-line gun	0.25 mm, 90° deflection, Ø29.1 mm in-line gun			
		Visual screen mm 4:3	491.3 (W) × 368.5 (H), (614.1)	361.6 (W) × 271.2 (H), (452)			
		(viewable area, measured diagonally)16:9	655.2 (W) × 368.5 (H), (751.7)	482.1 (W) × 271.2 (H), (553.1)			
		4:3 inches 16:9	$\frac{19\ {}^3/_8\times 14\ {}^5/_8,\ (24\ {}^1/_4)}{25\ {}^7/_8\times 14\ {}^5/_8,\ (29\ {}^5/_8)}$	$\frac{14 \frac{1}{4} \times 10 \frac{3}{4}, (17 \frac{7}{8})}{19 \times 10 \frac{3}{4}, (21 \frac{7}{8})}$			
		Phosphor	SMP				
Inputs/Outputs	Video	F	BNC × 3, with				
1		GBR	1.0 Vp-p ±6	· · ·			
		Y	1.0 Vp-p ±6 dB,				
		PB/PR	0.7 Vp-p ±6 dB,	high impedance			
	Ext sync		BNC × 1, with	loop-through			
		Composite	0.3 to 8.0 Vp-p, high imped	lance, tri-level bipolar sync			
	Remote	OPTION	RS-232C for BKM-11				
		CONTROL UNIT	RS-422 for BKM-1				
		REMOTE 1/Serial remote	RS-485 serial interface, D-su				
		REMOTE 2/Parallel remote 1	D-sub 9-pin × 1 (				
		Parallel remote 2	Not Ap	*			
Video signal	Differenti	ISR al gain (DC)	D-sub 9				
Video signal performance		al gain (DG) al phase (DP)	Within 5% for luminance from 0 to 70 cd/m²           Within 5° for luminance from 0 to 70 cd/m²	Within 5% for luminance from 0 to 100 cd/m²           Within 5° for luminance from 0 to 100 cd/m²			
			50 Hz to 30 MF				
Frequency response DC restoration			Back porch type, back porch level: withi				
Synchronization			under 3				
5		Vertical	under 6	•			
Raster and picture performance	Normal so	can	5% over scan of the e	effective picture area			
performance	Under sca	n	3% under scan of the	effective picture area			
	Linearity		Less than 1.0% within circle centered on the screen	Less than 0.5% within circle centered on the screen			
	Color tom	un anatuma	with a diameter equal to the vertical height, 2.0% at any other point* D65/D93/COL 1/CC				
	Color tem Converge	<u>.</u>	Less than 0.5 mm within circle centered on the screen	Less than 0.4 mm within circle centered on the screen			
	Converge	alce	with a diameter equal to the vertical height, 0.8 mm at any other point				
	Preset brig	ghtness	70 cd/m <sup>2</sup> (30 fL)	100 cd/m <sup>2</sup> (30 fL)			
		<b>0</b>	(when a 1.0 Vp-p 100% white signal is input)	(when a 1.0 Vp-p 100% white signal is input)			
	Stability o	of raster size	1.0% of picture height (at 70 cd/m <sup>2</sup> peak luminescence, 10 to 90% APL)	1.0% of picture height (at 100 cd/m <sup>2</sup> peak luminescence, 10 to 90% APL)			
	Scan delay	Horizontal	Approx.				
	5	Vertical	Approx.				
	Center res	solution	16:9 1000 TV lines				
Operating	Operating	g temperature	0 to 35°C (				
conditions	Storest	mporatura	Optimum operating rang -10 to 40°C (				
	Humidity	emperature	-10 to 40 C ( 0 to 90% (no c				
Others		accessories	AC cable, AC plug holder, Tally				
ouldis		n compliance	UL 1950/CSA 950 (cUL listed), FCC				
Dimensions (mm	0		CE TOUS (CE TUSS (CE TUSS ()) 1 CE	Calab T 1 0 0 0 0 0 1 0 0 1 0 0 0 0 0 0 0 0 0			
* 1080/60I and 1035/60	or						

BVM-D20F1U	BVM-D14H1U	BVM-D14H5U					
	15.625 kHz to 45 kHz (For more details, please refer to the Acceptable Formats table)						
Displ	ay unit	Stand-alone monitor					
	100 to 240 V AC ± 10%, 50/60 Hz						
150 W (210 W max.)	100 W (115 W max.)						
$444 (W) \times 414 (H) \times 570 (D)$	$346 (W) \times 280 (H) \times 519 (D)$	482 (W) × 280 (H) × 562 (D)					
$\frac{171/_2 \times 163/_8 \times 221/_2}{20 \log (0.021 \log 10^{-1})}$	$\frac{135/8 \times 111/8 \times 201/2}{11 \log (1000 \log 10^{-1})}$	$19 \times 11 \frac{1}{8} \times 22 \frac{1}{4}$					
approx. 38 kg (83 lb 10 oz) 20-inch HR Trinitron	approx. 21 kg (46 lb 3 oz)	approx. 23 kg (50 lb 10 oz)					
20-inch HR Trinitron     14-inch HR Trinitron       0.30 mm, 90° deflection, Ø 30.6 mm in-line gun     0.25 mm, 90° deflection, Ø 29.4 mm in-line gun							
386 (W) × 291 (H), (482)		00.6 (H), (331.6)					
386 (W) × 218 (H), (443)		i0.5 (H), (306.9)					
$\frac{15 \frac{1}{4} \times 11 \frac{1}{2}}{15 \frac{1}{4} \times 8 \frac{5}{8}}, (17 \frac{1}{2})$	$10^{5/8} \times 10^{5/8} \times 6.12$	8, (13 <sup>1</sup> / <sub>8</sub> ) <sup>2</sup> <sup>1</sup> / <sub>8</sub> )SMPTE-C					
	SMPTE-C						
BNC $\times$ 3, with loop-through	BNC $\times$ 3, with loop-through the second sec	ugh, 75 Ω auto terminated					
	1.0 Vp-p ±6 dB, positive						
	1.0 Vp-p $\pm 6$ dB, high impedance						
	0.7 Vp-p ±6 dB, high impedance						
BNC × 1, with loop-through	BNC × 1, with loop-throu 0.3 to 8.0 Vp-p, high impedance, tri-level bipolar sync	ugh, 75 Ω auto terminated					
	RS-232C for BKM-11R Mini DIN 8-pin						
RS-422 for BKM-	10R D-sub 9-pin	Not Applicable					
	RS-485 serial interface, D-sub 9-pin, with loop-through	rr					
	D-sub 9-pin $\times$ 1 (Short to ground)						
Not Applicable	Modular co	nnector 6-pin					
D-sub 9-pin × 1		pplicable					
	Within 5% for luminance from 0 to 100 cd/m <sup>2</sup>						
50 Hz to 30 MHz +1 dB/-3 dB	Within 5° for luminance from 0 to 100 cd/m <sup>2</sup>	Hz +0 dB/-3 dB					
	prch type, back porch level: within 1% of peak luminance, 10 to 9						
	under 3.77 µsec						
	under 650 µsec						
	5% over scan of the effective picture area						
	3% under scan of the effective picture area						
Less than 0.5% within circle centered on the screen with a diameter equal to the vertical height, 1.0% at any other point*		cle centered on the screen rtical height, 2.0% at any other point					
	D65/D93/COL 1/COL 2 (User adjustable)						
	Less than 0.4 mm within circle centered on the screen						
100 cd/m² (30 fL)	vith a diameter equal to the vertical height, 0.7 mm at any other po						
(when a 1.0 Vp-p 100% white signal is input)	120 cd/m² (35 fL) (when a 1.0 Vp-p 100% white signal is input)						
1.0% of picture height	1.0% of picture height						
(at 100 cd/m <sup>2</sup> peak luminescence, 10 to 90% APL) Approx. 3/8 line	(at 120 cd/m <sup>2</sup> peak luminescence, 10 to 90% APL) Approx. 1/4 line						
Approx. 9 8 line	Approx. 1/2 field	м -7 4 ШИС					
16:9 700 TV lines, 4:3 900 TV lines		s, <b>4:3</b> 800 TV lines					
	0 to 35°C (32 to 95°F)						
	Optimum operating range 20 to 30°C (68 to 86°F) -10 to 40°C (14 to 104°F)						
	-10 to 40 C (14 to 104 F) 0 to 90% (no condensation)						
4:3	mask AC cable, AC plug holder, Tally label, Fuse, Operation ma	nual					
	1950/CSA 950 (cUL listed), FCC Class-A/IC Class-A, DHHS/D						
	346 (13 <sup>5</sup> /8)						

# **Specifications**

			BVM-D9H1U	BVM-D9H5U			
General	Signal format		15.625 kHz to 45 kHz (For more details, please refer to the Acceptable Formats table)				
	Type		Display unit	Stand-alone monitor			
	51	uirements	100 to 240 V AC ± 10%, 50/60 Hz				
		sumption (with options)	60 W (with OPTION: 85 W max.)				
	Dimensio		$\begin{array}{c c c c c c c c c c c c c c c c c c c $				
		ll protruding parts) inches	$85/_8 \times 67/_8 \times 143/_8 (171/_4)$	8 5/8 × 8 5/8 × 15 (17 7/8)			
	Mass	i or incres	approx. 8.1 kg (17 lb 13 oz), 8.9 kg (19 lb 9 oz)*2	approx. 9.3 kg (20 lb 7 oz), 10.1 kg (22 lb 4 oz) $^{*2}$			
	CRT	CRT type	9-inch HR				
	OIII	AG pitch	0.25 mm, 70° deflection				
		Visual screen mm 4:3	155.4 (W) × 1	0			
		(viewable area, measured diagonally) 16:9	155.4 (W) × 8				
		inches 4:3	6 1/8 × 4 5	/ <sub>8</sub> , (7 <sup>5</sup> / <sub>8</sub> )			
		16:9	6 1/8 × 3 1	/2, (71/8)			
		Phosphor	P-	22			
Inputs/Outputs	Video		BNC $\times$ 3, with loop-throu	gh, 75 Ω auto terminated			
		GBR	1.0 Vp-p ±6	dB, positive			
		Y	1.0 Vp-p ±6 dB,	high impedance			
		PB/PR	0.7 Vp-p ±6 dB,	high impedance			
	Ext sync		BNC × 1, with loop-throu	gh, 75 Ω auto terminated			
		Composite	0.3 to 8.0 Vp-p, high imped	lance, tri-level bipolar sync			
	Remote	OPTION		IR Mini DIN 8-pin			
		CONTROL UNIT	D-sub 9-pin (RS-485/422 switchable)	Not Applicable			
		REMOTE 1/Serial remote	RS-485 serial interface, D-su	ub 9-pin, with loop-through			
		REMOTE 2/Parallel remote 1		D-sub 9-pin × 1 (Short to ground)			
		Parallel remote 2	Modular connector 6-pin				
	ISR		Not Applicable				
Video signal	Differentia	al gain (DG)	Within 5% for luminance from 0 to 100 cd/m <sup>2</sup>				
performance	Differential phase (DP)		Within 5° for luminance from 0 to 100 cd/m <sup>2</sup>				
	Frequency response		48 Hz to 17 MF	Hz +0 dB∕-3 dB			
	DC restor		Back porch type, back porch level: withi	n 1% of peak luminance, 10 to 90% APL			
Synchronization	Retrace time	Horizontal	under 3.77 µsec				
		Vertical	under 650 µsec				
Raster and picture	Normal se	an	5% over scan of the effective picture area				
performance	Under scan		3% under scan of the effective picture area				
	Linearity		Less than 2.0% within circle centered on the screen with a diameter equal to the vertical height				
	Color tem	perature	D65/D93/COL 1/CO				
	Converge	nce	Less than 0.4 mm within circle centered on the screen with a diameter equal				
			to the vertical height, 0.7 mm at any other point				
	Preset brightness		120 cd/m² (35 fL) (when a 1.0 V	/p-p 100% white signal is input)			
	Stability o	f raster size	1.0% of picture height (at 120 cd/m <sup>2</sup> peak luminescence, 10 to 90% APL)				
	Scan delay	Horizontal	Approx. 1/4 line				
		Vertical	Approx.	<sup>1</sup> / <sub>2</sub> field			
	Center res	olution	16:9 340 TV lines, 4:3 450 TV lines				
Operating condition	s Operating	temperature	0 to 35°C (32 to 95°F)				
	~		Optimum operating rang	·			
	0	mperature	-40 to 40°C				
	Humidity		0 to 90% (no d				
Others		accessories	4:3 mask, AC cable, AC plug holder, AC				
	Regulation	n compliance	UL 1950/CSA 950 (cUL listed), FCC	Class-A/IC Class-A, DHHS/DNHW			
Dimensions (mm)							

\*1 Depth with AC adaptor \*2 Mass with AC adaptor

**Distributed by** 

© 2000 Sony Electronics, Inc. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. All non-metric weights and measures are approximate. Sony and Trinitron are registered trademarks of Sony Corporation.

Sony Electronics, Inc. 1 Sony Drive Park Ridge, NJ 07656

MK7317V3TC00MAR V-11109