Optical Attenuator (variable)

OLA-15





OLA-15

for single-mode applications at 1310 and 1550 nm

- Wide range of applications in systems installation and maintenance, as well as production
- Large, continuously variable attenuation range
- Attenuation settings highly accurate and reproducible
- High return loss
- Universal interchangeable adapter system
- Rugged shock and water-resistant casing
- AC, dry- or rechargeable battery operation

Wide range of applications in systems installation and maintenance, as well as production

The OLA-15 Optical Attenuator is a handy-sized, rugged instrument for variably attenuating optical signals in single-mode applications at 1310 and 1550 nm. Example applications include the simulation of line loss for BER tests on fiber optics systems, the determination of system margin / receiver sensitivity or the calibration of optical power meters. A complete test set comprising signal source, attenuator and power meter contained in a shock-resistant case is also available.

Large, continuously variable attenuation range

The large rotary control on the front panel is used to set attenuation quickly and simply within a wide range between 3 and 60 dB.

The optical path is not interrupted when the attenuation is altered. As the OLA-15 is bidirectional, the instrument is very easy to use.

Attenuation settings highly accurate and reproducible

Reliable measurements demand accuracy and reproducibility of the attenuation setting. Each instrument is individually calibrated, guaranteeing that every OLA-15 meets this requirement. Careful design of the optical components ensures interference-free attenuation settings over the entire temperature range. The attenuation setting is indicated on a large liquid-crystal display.

High return loss

The OLA-15 is also suitable for measurements on systems sensitive to back-reflection, e.g. those operating at high bit rates. The return loss (reflection attenuation) of more than 40 dB means that the OLA-15 can be looped into the signal path without problems and without affecting the transmission characteristics.

Universal interchangeable adapter system

The universal system of interchangeable adapters allows matching to all commonly-used fiber optics connector systems, such as FC, SC and DIN. It also ensures easy access to the instrument's internal connectors for the purposes of cleaning and inspection. Special dust caps protect the optical connectors from dirt and damage.

Australia: Tel. +61-3-9690 6700 Brazil: Tel. +55-11-5503 3800 China: Tel. +86-10-8809 1288 Singapore: Tel. +65-377-3003 United Kingdom: Tel. +44-1189-409200 USA: Tel. +1-919-941-5730 Worldwide: Tel. +49-7121-86 16 16 \cdot Fax +49-7121-86 13 33 E-mail: info@wwgsolutions.com http://www.wwgsolutions.com

Rugged shock and water-resistant casing

The instrument is protected against shocks and wear and tear by a well-designed, non-slip, robust casing, giving the OLA-15 the mechanical ruggedness required for field use under often difficult ambient conditions. The foil keypad gives protection against dripping water. A fold-out instrument stand is located on the back panel.

AC line or long-life battery operation

The Optical Attenuator is designed for use with dry batteries or with NiCd cells. Typical operating time from dry batteries is 45 hours; a set of NiCd cells will run for typically 15 hours, more than a day of uninterrupted operation. When a separate AC adapter is used, the instrument can be AC powered and NiCd batteries fitted in the instrument can also be recharged.

Specifications for the Optical Attenuator

OLA-15

Wavelength Range of use	General specifications Power supply Dry batteries 2 × Mignon (AA) 1.5 V NiCd rechargeable batteries 2 × Mignon (AA) 1.2 V	
	Operating time (typical)	
Attenuation display	Ambient temperature Nominal range of use5 to +55° Storage and transport40 to +70° Dimensions (w×h×d) in mmapprox. 95×49×19	
Optical input/output Interchangeable adapter BN 2060/00.xx	Weight (including batteries) approx. 500 g 1) Including connectors (to IEC 874-1, Method 6) 2) Excluding remating 3) Typical value; depends on the characteristics of the external plug	

Ordering information

OLA-15 Optical Attenuator ¹⁾	BN 2239/01	Carrying Strap Cleaning tape for optical connectors	BN 820/00.52 BN 2229/90.07	
		MK-1 Equipment Case	BN 2090/13	
Options		(Hard-shell case for 2 instruments plus accessories)	DN 0400/04	
Calibration report for OLA-15	BN 2239/90.01	MT-2 Instrument Bag	BN 2126/01	
		(Soft-carrying bag for 2 instruments plus accessories)		
Accessories		MT-32 Instrument Bag	BN 2126/32	
Test adapters	BN 2060/00.xx	(Soft-carrying bag for 1 × OLX-1x and 2 × OLX-x and accessories)		
NiCd cell, Mignon (AA) type ²⁾	BN 2229/90.02	ABK-30 Storage Case (for storing adapters, cables and other accessories)	BN 2126/30	
Battery Charger (for external charging)	2.12220,00102			
220 V. Euro-style plug	BN 2229/90.03	Detailed information on adapters, cables and fiber optics couplers is found in the separate data sheet "Fiber Optics Test		
110 V, US-style plug	BN 2229/90.09			
NT-20 AC Adapter	DIV 2223/30.03	Adapters and Cables".		
EURO Version	BN 2238/90.02			
		 Two adapters BN 2060/00.xx are included with each instrument (except for bare fiber adapter BN 2060/00.39). Specify type required when ordering. 		
UK Version	BN 2238/90.03			
US Version	BN 2238/90.04			
Australian Version	BN 2238/90.05	2) Two required.		

 $Subject\ to\ change\ without\ notice\ -\ E/0296/D1/843/5.0\ GN\ v.\ 792\ -\ Printed\ in\ the\ Federal\ Republic\ of\ Germany$





